

Petite Fleur-eo



Refrigerated Heating Circulator with air-cooled refrigerating unit. Powerful, variable speed pump, housing of stainless steel, CFC and H-CFC free. Speed controlled pump (soft start), pump pressure control. With adjustable overtemperature protection according to DIN 12876.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

3-2-2 warranty - registration required.

Please note

The machine is developed exclusively for external open operation, and does not possess an expansion tank. The filling of the thermofluid, and allowance for the temperature dependent volume changes is only possible via an externally connected application.

Technical data according to DIN 12876

Operating temperature range Temperature stability at -10°C temperature set point / display Resolution of display Internal temperature sensor Sensor external connection Interface digital

digital input digital output Alarm message Safety classification Heating power at 240V Heating power at 230V Heating power at 220V Cooling power with

at 200°C
at 150°C
at 100°C
at 50°C
at 20°C
at 0°C
at -20°C
at -30°C
at -40°C

Refrigeration machine

Pump connection

Refrigerant (ASHRAE, GHS) Refrigerant quantity Gas warning sensor Circulation pump: max. delivery max. delivery pressure -40...200 °C 0.01 K

5,7" colour Touchscreen

0,01 K Pt100 Pt100

Ethernet, USB (Host u. Device), RS232 ECS ONE

POKO ONE

optic, acoustic, relay

III / FL 2 kW 1,8 kW 1,6 kW Thermooil 0,48 kW 0,48 kW 0,48 kW 0,48 kW 0,48 kW 0,48 kW 0,48 kW

0,16 kW 0,04 kW air-cooled, natural

refrigerant R290 (A3, H220)

0,08 kg without

25 l/min 0,9 bar M16x1 male



Order-No.: 1030.0004.01

Technical data according to DIN 12876

from Serial-No.:	403222	1.3/21
max. ambient temperature	40 °C	
min. ambient temperature	5 °C	
Degree of Protection	IP20	
Fuse Pressure equipment category	16 A 4.3 PED	
max. current	11,5 A	
Power supply requirement	220-240V 1~/2~ 50/60Hz	
sound pressure level +/- 4 dB(A)	58 dB(A)	
Net weight	45 kg	
Overall dimensions WxDxH **	260x450x504 mm	
min. filling capacity	21	
max. permissible kin. viscosity	50 mm ² /s	

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: mini-USB cable #54949*, E-grade "Professional" #9496*, E-grade "Explore" #10495, Adapter nom. dia. 12*, sleeve nuts M16x1 male*, Com.G@te Namur

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed! -5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

^{*} standard equipment